

SDR(Silicone Decoration Ring)

Patent pending

We present the silicone ring that is available for general full-rim frames. Taking advantage of the flexibility of silicone, just this one SDR can be used on ALL full-rim frames. In addition, it can eliminate lens distortion. SDR achieves two things at the same time.




Features of SDR




It can be used for the general V groove of a full-rim frame.

SDR35




It can be fitted for ALL lens shapes because it is made from silicone.




Please make the lens cut with a regular half-rim cut.

SDR35 : $\Phi 35 \times 1.8\text{mm}$



cross section



3 benefits

1. You can easily create new added value in design.
2. Just this one SDR can be used on ALL full-rim frames.
3. The SDR acts as cushioning material and eliminates lens distortion.

How to attach?

<https://youtu.be/Mt1LVawMv20>



Color variations



C1: Black




C2: Gray



C3: Clear



C4: Sky blue



C5: Blue



C6: Moss green



C7: Brown



C8: Pink



C9: Red



C10: Bordeaux